


SonTek Instrumentation Accessories List

Need replacement parts or accessories for your SonTek gear? Use this handy color-coded checklist to help get you started! Find quick access to part-numbers and cost-per-item.

Once you have identified what you need, you can place your order via one of our friendly Customer Support Specialists at sontek.orders@xylem.com. Or, call +1.858.546.8327, option 3.

ADP SPARE PARTS  	ADP 19-0024 \$80 Power supply, 24VDC, 60 Watt, ADP/ADV 	ADP 2885-00103 \$10 Power cord (U.S.) 
ADP 2885-00125 \$35 Power cord kit (International) 	ADP 36-0013-010 \$950 10-m power and RS232 communications cable, 8-pin male wet pluggable to 9-pin D-sub 	ADP 36-0050-002 \$1,010 Splitter cable, to connect ADP with external battery case (standard, 2-m length) 

ADP 6048-08100 \$130 Connector, 8-pin male wet pluggable dummy plug (DC-8-MP) 	ADP 6048-95000 \$30 Locking Sleeve for standard wet-pluggable connectors, male 	ADP 6052-00033 \$300 Battery Pack, alkaline, 18V, 36D, ADP/ADV 
ADP AK3 \$20 Zinc Anode standard aluminum ADP systems (requires 5 per system for 250/500 kHz ADP, 4 per system for 250/500 kHz SL-ADP, 2 per system for 1.0 MHz ADP) 	ADP 6053-00045 \$120 Tool kit for Standard ADP 	ADP 6053-00046 \$150 Tool kit for Standard ADP (PP) 
ADP 6053-00087 \$120 Tool kit for ADP/ADV fiberwound plastic electronics/battery housing 	Argonaut-ADV SPARE PARTS 	Argonaut-ADV 19-0022 \$75 Power supply, 15VDC, 40W 
Argonaut-ADV 2885-00103 \$10 Power cord (U.S.) 	Argonaut-ADV 2885-00125 \$35 Power cord kit (International) 	Argonaut-ADV 36-0008-010 \$830 10-m power and RS232/SDI12 communications cable, compact 8-pin male wet pluggable to 9-pin D-sub, 8-conductor 

Argonaut-ADV 36-0008-040 \$1,135 40-m power and RS232/SDI12 communications cable, compact 8-pin male wet pluggable to 9-pin D-sub, 8-conductor 	Argonaut-ADV 36-0052-001 \$1,000 1-m Splitter cable for SL/SW/Triton to external battery housing 	Argonaut-ADV 6048-08140 \$110 Connector, compact 8-pin male wet-pluggable dummy plug (MCDC-8-MP) 
Argonaut-ADV 6048-95010 \$20 Locking Sleeve for compact wet-pluggable connector, female 	Argonaut-ADV 6052-00050 \$135 Battery Pack, alkaline, 10.5V, 21C, Triton/Argonaut-ADV 	Argonaut-ADV AK2 \$85 Zinc anode with hardware, ADV with 1/2 inch stem (10 MHz ADV/Triton/Argonaut-ADV) 
Argonaut-ADV 6053-00175 \$80 Tool kit for Argonaut-ADV/Triton-ADV 	Argonaut-XR SPARE PARTS 	Argonaut-XR 19-0022 \$75 Power supply, 15VDC, 40W 
Argonaut-XR 2885-00103 \$10 Power cord (U.S.) 	Argonaut-XR 2885-00125 \$35 Power cord kit (International) 	Argonaut-XR 36-0015-010 \$1,065 10-m power and RS232/SDI-12 communications cable, Flow Display capable, 8-pin male wet-pluggable to 9-pin D-sub, 12 conductor 


Argonaut-XR 36-0015-040 \$1,930 40-m power and RS232/SDI-12 communications cable, Flow Display capable, 8-pin male wet-pluggable to 9-pin D-sub, 12 conductor 	Argonaut-XR 36-0015-070 \$2,680 70-m power and RS232/SDI-12 communications cable, Flow Display capable, 8-pin male wet-pluggable to 9-pin D-sub, 12 conductor 	Argonaut-XR 36-0015-100 \$3,430 100-m power and RS232/SDI-12 communications cable, Flow Display capable, 8-pin male wet-pluggable to 9-pin D-sub, 12 conductor 
Argonaut-XR 36-0053-001 \$1,185 1-m Splitter cable for Argonaut-XR with external battery housing 	Argonaut-XR 6048-08100 \$130 Connector, 8-pin male wet pluggable dummy plug (DC-8-MP) 	Argonaut-XR 6048-95000 \$30 Locking Sleeve for standard wet-pluggable connectors, male 
Argonaut-XR 6052-00051 \$205 Battery Pack, alkaline, 12V, 24D, XR/SL/Triton 	Argonaut-XR 6053-00067 \$80 Toolkit for XR 	Argonaut-XR 6053-00068 \$250 Tool kit for XR with external battery case 
Argonaut-XR 7371-00125 \$60 Mounting plate, Argonaut-XR and old-style Argonaut-SL, without battery 	Argonaut-XR 7371-00126 \$125 Mounting plate for Argonaut-XR with external battery housing 	CastAway - CTD SPARE PARTS  


CastAway-CTD 28-0096 \$80 Stylus Kit. Includes stylus and lanyard 	CastAway-CTD 28-0097 \$170 Jacket Kit. Includes CastAway-CTD jacket and (1) caribiner 	CastAway-CTD 28-0098 \$9 Maintenance Pack. Includes cleaning brush, lubricant, o-ring 
CastAway-CTD 40-0011 \$70 Bluetooth adapter, USB 	CastAway-CTD 400309 \$200 CastAway-CTD plastic shipping case 	CastAway-CTD 400312 \$10 Caribiner 
FLOWTRACKER 2 SPARE PARTS  	FlowTracker 2 FT2-MR \$1,625 2-piece top-setting wading rod, 1.2-m, metric increments in cm; bubble level, mounting brackets for FT2 Display unit and ADV sensor, and plastic shipping case 	FlowTracker 2 FT2-ER \$1,625 2-piece top-setting wading rod, 4-ft, English increments in tenths of ft; bubble level, mounting brackets for FT2 Display unit and ADV sensor, and plastic case 
FlowTracker 2 24-0324 \$195 Wading rod offset mounting bracket for FlowTracker ADV Sensor, for hex-shaped wading rod 	FlowTracker 2 24-0066 \$190 Wading rod mounting bracket for FlowTracker ADV sensor, for SonTek round wading rod 	FlowTracker 2 28-0148 \$220 Wading rod offset mounting bracket for FlowTracker ADV sensor, for 20-mm universal wading rod 



FlowTracker 2 24-0314 \$700 Plastic shipping case only, FlowTracker2 with 1.2-m/4-ft wading rod 	FlowTracker 2 24-0313 \$450 Plastic shipping case, FlowTracker2 	FlowTracker 2 28-0137 \$70 Battery holder, 8 AA cells (for Handheld Display Unit) 
FlowTracker 2 28-0146 \$200 Wading rod mounting clamp, FlowTracker2 Handheld Display unit 		FlowTracker 2 28-0149 \$185 20-mm universal wading rod adapter for the FlowTracker2 Handheld Display unit wading rod mounting clamp (P/N 28-0146) 
FlowTracker 2 31-0033 \$30 Cable, USB to MicroUSB, 6-ft 	FlowTracker 2 36-0039-001 \$715 1.5-m FlowTracker2 ADV sensor extension cable, compact 8-pin male to compact 8-pin female wet-pluggable 	FlowTracker 2 36-0039-003 \$750 3.5-m FlowTracker2 ADV sensor extension cable, compact 8-pin male to compact 8-pin female wet-pluggable 
FlowTracker 2 36-0039-008 \$875 8.5-m FlowTracker2 ADV sensor extension cable, compact 8-pin male to compact 8-pin female wet-pluggable 	FlowTracker 2 36-0049 \$1,325 Splitter cable, for connecting FlowTracker2 probe assembly to computer and power supply 	S5/M9/PCM2 SPARE PARTS 

S5/M9/PCM2 -River/HydroSurveyor 10-0147 \$1,250 DGPS / RTK GPS antenna 	S5/M9/PCM2 -River/HydroSurveyor 10-0673 \$15 2.4-GHz antenna (2 dBi) 	S5/M9/PCM2 -River/HydroSurveyor 10-0696 \$130 Battery charger, 16 position, for AA NiMH batteries 
S5/M9/PCM2 -River/HydroSurveyor 10-0697 \$125 Rechargeable NiMH AA batteries, package of (16) 	S5/M9/PCM2 -River/HydroSurveyor 19-0011 \$175 Power Supply, 18VDC 	S5/M9/PCM2 -River/HydroSurveyor 19-0017 \$325 2.4 GHz USB radio 
S5/M9/PCM2 -River/HydroSurveyor 20-0235 \$10 Right angle adapter, TNC male to TNC female 	S5/M9/PCM2 -River/HydroSurveyor 20-0236 \$10 Adapter, SMA female to TNC male 	S5/M9/PCM2 -River/HydroSurveyor 24-0032 \$110 RiverSurveyor S5/M9 GPS antenna support rod mounting bracket 
S5/M9/PCM2 -River/HydroSurveyor 28-0177-01 \$50 PCM battery slot endcap, Square Battery Holder 	S5/M9/PCM2 -River/HydroSurveyor 28-0177-02 \$50 PCM battery slot endcap, Round Battery Holder 	River/HydroSurveyor S5/M9 & PCM 24-0246 \$110 Radio antenna mounting bracket for use with GPS antenna support rod 

River/HydroSurveyor S5/M9 & PCM 24-0247 \$50 Tripod spacer for GPS antenna support rod 	River/HydroSurveyor S5/M9 & PCM 28-0110 \$205 Battery holder, 8 AA cells, Round Battery holder slot. 	River/HydroSurveyor S5/M9 & PCM 28-0137 \$70 Battery holder, 8 AA cells Square battery holder slot 
River/HydroSurveyor S5/M9 & PCM 31-0020-02 \$70 Radio antenna extension cable, 2-ft 	River/HydroSurveyor S5/M9 & PCM 31-0020-10 \$90 Radio antenna extension cable, 10-ft 	River/HydroSurveyor S5/M9 & PCM 31-0021-02 \$70 GPS antenna cable, 2-ft. 
River/HydroSurveyor S5/M9 & PCM 31-0021-10 \$80 GPS antenna cable, 10-ft. 	River/HydroSurveyor S5/M9 & PCM 36-0000-001 \$620 1-m power & RS232 serial communications cable, compact 8-pin female to compact 8-pin male wet-pluggable 	River/HydroSurveyor S5/M9 & PCM 36-0000-010 \$620 10-m power & RS232 serial communications cable, compact 8-pin female to compact 8-pin male wet-pluggable 
River/HydroSurveyor S5/M9 & PCM 36-0001-010 \$700 10-m power & RS232 serial communications cable, compact 8-pin male wet-pluggable to 9-pin D-sub 	River/HydroSurveyor S5/M9 & PCM 36-0001-030 \$1,010 30-m power & RS232 serial communications cable, compact 8-pin male wet-pluggable to 9-pin D-sub 	River/HydroSurveyor S5/M9 & PCM 40-0005 \$10 Power cord (U.S.) 

River/HydroSurveyor S5/M9 & PCM 40-0008 \$60 Power cord kit, (International) 	River/HydroSurveyor S5/M9 & PCM 6045-00800 \$65 GPS Antenna Support Rod 	SL1500-3G / SL3000-3G 
SL1500-3G/SL3000-3G 19-0012 \$105 Cable Adaptor. Connects the instrument to power, SDI-12, Modbus, allows interface to laptop PC. 	SL1500-3G/SL3000-3G 19-0013 \$70 Power Supply. Input 100/240VAC, output 12 VDC 	SL1500-3G/SL3000-3G 24-0273 \$85 Mounting plate, SonTek-SL1500-3G/3000-3G 
SL1500-3G/SL3000-3G 28-0106 \$105 Dummy Plug Kit, (1) 5-pin male dry-pluggable connector and (1) 5-pin female dry-pluggable connector 	SL1500-3G/SL3000-3G 28-0128 \$160 Tool Kit, SL1500-3G 	SL1500-3G/SL3000-3G 31-0015 \$25 Battery hook-up cable, 5ft (1.5m) 
SL1500-3G/SL3000-3G 36-0040-010 \$340 10-m power and RS232/SDI-12/Modbus communications cable, compatible with the SonTek-IQ Flow Display, 5-pin male dry-pluggable to terminal block 	SL1500-3G/SL3000-3G 36-0040-020 \$450 20-m power and RS232/SDI-12/Modbus communications cable, compatible with the SonTek-IQ Flow Display, 5-pin male dry-pluggable to terminal block 	SL1500-3G/SL3000-3G 36-0040-040 \$720 40-m power and RS232/SDI-12/Modbus communications cable, compatible with the SonTek-IQ Flow Display, 5-pin male dry-pluggable to terminal block 

SL1500-3G/SL3000-3G 36-0040-060 \$975 60-m power and RS232/SDI-12/Modbus communications cable, compatible with the SonTek-IQ Flow Display, 5-pin male dry-pluggable to terminal block 	SL1500-3G/SL3000-3G 36-0040-100 \$1,475 100-m power and RS232/SDI-12/Modbus communications cable, compatible with the SonTek-IQ Flow Display, 5-pin male dry-pluggable to terminal block 	SL1500-3G/SL3000-3G 36-0043 \$1,050 1-m Splitter cable for SonTek-SL1500-3G/3000-3G to external battery housing 
SL500 SPARE PARTS 	SL500 19-0022 \$75 Power supply, 15VDC, 40W 	SL500 2885-00103 \$10 Power cord (U.S.) 
SL500 2885-00125 \$35 Power cord kit (International) 	SL500 36-0003-010 \$815 10-m power and RS232/SDI-12 communications cable, Flow Display capable, 8-pin male wet-pluggable to 9-pin D-sub 	SL500 36-0003-040 \$1,300 40-m power and RS232/SDI-12 communications cable, Flow Display capable, 8-pin male wet-pluggable to 9-pin D-sub 
SL500 36-0003-070 \$1,850 70-m power and RS232/SDI-12 communications cable, Flow Display capable, 8-pin male wet-pluggable to 9-pin D-sub 	SL500 36-0003-100 \$2,350 100-m power and RS232/SDI-12 communications cable, Flow Display capable, 8-pin male wet-pluggable to 9-pin D-sub 	SL500 36-0009-001 \$1,025 1-m Splitter cable for SL/SW/Triton to external battery housing 

SL500 6048-08140 \$110 Connector, compact 8-pin male wet-pluggable dummy plug (MCD8-8-MP) 	SL500 6048-95010 \$20 Locking Sleeve for compact wet-pluggable connector, female 	SL500 6052-00051 \$205 Battery Pack, alkaline, 12V, 24D, XR/SL/Triton 
SL500 7371-00151 \$130 Mounting plate for SL500 (without external battery housing) 	SL500 7371-00152 \$130 Mounting plate for SL500 and external battery housing 	SonTek IQ SPARE PARTS 
SonTek-IQ 19-0012 \$105 Cable Adaptor. Connects the instrument to power, SDI-12, Modbus, allows interface to laptop PC. 	SonTek-IQ 19-0013 \$70 Power Supply. Input 100/240VAC, output 12 VDC 	SonTek-IQ 28-0091 \$75 SonTek IQ Spare Parts Kit. Mounting brackets, 8 mounting bracket screws, two 5-pin and two 3-pin connectors for the SonTek-IQ cable adaptor. 
SonTek-IQ 28-0093 \$115 Tool Kit, SonTek-IQ systems 	SonTek-IQ 28-0106 \$105 Dummy Plug Kit, (1) 5-pin male dry-pluggable connector and (1) 5-pin female dry-pluggable connector 	SonTek-IQ 31-0015 \$25 Battery hook-up cable, 5ft (1.5m) 

SonTek-IQ 36-0040-010 \$340 10-m power and RS232/SDI-12/Modbus communications cable, compatible with the SonTek-IQ Flow Display, 5-pin male dry-pluggable to terminal block 	SonTek-IQ 36-0040-020 \$450 20-m power and RS232/SDI-12/Modbus communications cable, compatible with the SonTek-IQ Flow Display, 5-pin male dry-pluggable to terminal block 	SonTek-IQ 36-0040-040 \$720 40-m power and RS232/SDI-12/Modbus communications cable, compatible with the SonTek-IQ Flow Display, 5-pin male dry-pluggable to terminal block 
SonTek-IQ 36-0040-060 \$975 60-m power and RS232/SDI-12/Modbus communications cable, compatible with the SonTek-IQ Flow Display, 5-pin male dry-pluggable to terminal block 	SonTek-IQ 36-0040-100 \$1,475 100-m power and RS232/SDI-12/Modbus communications cable, compatible with the SonTek-IQ Flow Display, 5-pin male dry-pluggable to terminal block 	RS5 SPARE PARTS  
RS5 RS5-BATT \$50 Rechargeable Li-Ion Batteries, 3.7VDC 9.6WH, quantity of (2) 	RS5 19-0031 \$245 Bluetooth USB radio, RS5 	RS5 19-0033 \$30 Power supply for Li-Ion battery charger 
RS5 31-0043 \$30 Radio antenna extension cable, 2-ft (61-cm) 	RS5 31-0045 \$45 Radio antenna extension cable, 3-ft (90-cm) 	RS5 31-0048-01 \$385 GNSS antenna interface cable, 1-ft (30-cm) 

RS5	RS5	RS5
31-0048-02 \$385	40-0015 \$40	70-0054 \$30
GNSS antenna interface cable, 3-ft (90-cm)	Battery charger for Li-Ion battery packs	2.4-GHz antenna (2 dBi)
		